

8 7 6 5 4 3 2 1

D  
C  
B  
A

D  
C  
B  
A

Leave adequate clearance  
to ceiling for filter changes

Mist-Fit MF-1950

Access Door  
Leave adequate clearance  
for filter change

Hex Nut 1/4"-20 (x18)

Sealing Washer 1/4" (x18)

Panel Stiffener (x2)

CNC Machine Side

Side Mount

Hex Bolt 1/4"-20 (x8)  
with 1/4" Sealing Washer

Chip Strainer, Optional

Hex Bolt 1/4"-20 (x18)

Side Mount 19.5" w x 36" h

Drill clearance holes for 1/4" bolts  
in a suitable location  
use Side Mount as a template

Cut a 12 inch diameter hole  
to suit the Side Mount  
if no machine knock out is provided

Apply a sealant  
to mating surface  
if required




**AEROEX** Aeroex Technologies Inc.  
17 Hamilton Road  
Barrie, On L4N 8Y6  
Tel. 705-734-0199

Title: **Installation, MF-1950, Side Mount**

Dwg. No. **M20MBD-0014-B** Size **B**

Date: April 29, 2019 Drawn: T.B. Do not scale drawing Sheet 1 of 1

8 7 6 5 4 3 2 1



**AEROEX** Aeroex Technologies Inc.  
 17 Hamilton Road  
 Barrie, On L4N 8Y6  
 Tel. 705-734-0199

Title: Mist-Fit MF-1950 with Side Mount

Dwg. No. MF-1950-0014-B Size **B**

Date: April 22, 2019	Drawn: T.B.	Do not scale drawing	Sheet 1 of 1
----------------------	-------------	----------------------	--------------